


# AI Single Key Access Interlock




The AI is a single key access interlock ideal for use on hinged doors. The interlock has an open cavity design manufactured in either aluminium alloy/brass or stainless steel. Typical industries using the AI are food, chemical, pharmaceutical, mining, steel and power generation.

## OPERATION

The Castell single key access interlocks are used in various applications to control part body access to hazardous areas.


### AI single key access interlock (bolt trapped - key free)

#### 1 Key is free, bolt is trapped



While the key is free, the bolt of the AI is trapped in the mechanism. The door is locked.

#### 2 Insert and turn key, then turn and release bolt



By inserting and turning the key in the AI, the bolt is then free to be turned and released, which will trap the key in the lock.

#### 3 Key is trapped, bolt is unlocked



The key stays trapped while the bolt is released and the door is open.

## USAGE

The AI Access Interlock should be used to allow safe access to potential hazardous and dangerous areas.

The AI Access Interlock should be used on part body access doors where the use of personal safety keys is not essential (to prevent accidental lock in).

 The AI Access Interlock is not designed for security purposes, such as external access to a building.

No hazardous substances were used in the manufacture of this product. The product can be disposed of in standard waste.

## INSTALLATION


The housing of the AI access interlock should normally be mounted on the static frame of the guard and the bolt to the sliding or hinged door using suitable fasteners. Fixed bolt bracket is highly tolerant to misaligned guards and should be fitted with suitable fasteners. Please refer to the drawing on page 4 for mounting details for the housing and bolt. The AI interlocks are available in Hand 1 and Hand 2 version suitable for left or right hinged doors, respectively. Anti vibration pads should be used on machines that generate a high level of vibration.


 **IMPORTANT:** The AI Access Interlock should be mounted on the guard using anti-tamper fasteners to prevent unauthorised removal.

 You must use M6 anti-tamper stainless steel screws secured using threadlock set to a torque of 5N/M.

 Alignment limits of 0.5mm must be set in all planes. Angular displacement +/- 1° between lock and bolt.

 The AI Access Interlock must be installed by a competent and qualified person who has read and understood these instructions. Please retain this document in your technical file.

 The manufacturer should be consulted when use in a corrosive environment is planned.

 Use middle strength threadlock on all four switch lid fixing screws and tighten to a torque of 5 N/M to retain IP65 rating.

## MAINTENANCE

Periodic visual checks should be carried out by the site manager/safety officer.

Do not lubricate lock barrel with oil or grease, use CK Dry Powder Graphite if necessary.

 The interlock must be inspected every 6 months. Safety checks should include ensuring the keys and lock bolt can only be removed in the correct safety operating conditions (see page 1).

 In case of defects being detected please contact your nearest Castell Support Department for further actions. Please see Contact section for contact details.

## TECHNICAL DATA


<b>Temperature rating</b>	Minimum: -40°C [-40°F] ice free for Q & FS lock type
	Maximum: 107°C [224.6°F] for Q lock type/140°C [284°F] for FS lock type
<b>Type of mounting</b>	Surface mount using M6 stainless steel anti-tamper fasteners
<b>Weight</b>	Brass: 0.8 kg
	Stainless steel: 1.0 kg
<b>Material</b>	Aluminium alloy/brass or stainless steel
<b>Operation</b>	Suitable for 1,000,000 operations.
<b>B10d</b>	1,250,000
<b>Retention force</b>	3.4 KN
<b>PL rating</b>	PLd

## APPLICATION

A typical application of the AI Single Key Access Interlock is machine guarding with part body access.

The AI safety component is used as part of an integrated safety system, which ensures a machine is shut down, before access to the hazardous area is allowed.

This system involves a KS key switch that breaks the machine safety circuit, when the key is removed. The key may then be inserted into the AI Access Interlock to enable access to the machine. The machine cannot be restarted until the door is closed, the bolt is replaced and the key is then removed and returned to the KS key switch.



## EC-DECLARATION

We, the manufacturers, declare that the components detailed herein and placed on the market comply with all the essential health and safety requirements applying to them.

ISO 13849-1:2015 Safety of Machinery

2006/42/EC Machinery Directive

Empowered signatory:

Kirstie Van Oerle  
Business Unit Director




## DRAWING

Dimensions: in mm

**Note:** For safe mounting, use security screws



### AI, Hand 2



## ORDER INFORMATION


	<b>Component type</b>	<b>1</b>	<b>2</b>	<b>3</b>	<b>4</b>
Part number	AI				
Example	AI	FS	AL	1	ABC

<b>1</b>	<b>Lock portion type</b>	FS <sup>(1)</sup> / Q <sup>(1)</sup>
<b>2</b>	<b>Material</b>	AL = Aluminium alloy/brass S = Stainless steel
<b>3</b>	<b>Handing</b>	1 = left hinged door (bolt enters left) <sup>(2)</sup> 2 = right hinged door (bolt enters right) <sup>(2)</sup>
<b>4</b>	<b>Lock portion symbol</b>	FS <sup>(1)</sup> up to 3 characters / Q <sup>(1)</sup> up to 6 characters



Special construction available upon enquiry

## ACCESSORIES

	<b>Product</b>	<b>Part number</b>
	Flip Cap	FLIP-S

## CONTACT INFORMATION

### Castell Safety

The Castell Building  
217 Kingsbury Road  
London, NW9 9PQ  
UK

t: +44 (0)20 8200 1200  
f: +44 (0)20 8205 0055  
e: [sales@castell.com](mailto:sales@castell.com)

### Castell Safety

Tower 185  
60185 Frankfurt am Main  
Germany

t: +49 (0)69 50 50 47 310  
f: +49 (0)69 50 50 47 450  
e: [vertrieb@castell.com](mailto:vertrieb@castell.com)

### Kirk Key Interlock

9048 Meridian Circle NW  
North Canton, OH 47720  
USA

t: +1 800 438 2442  
f: +1 330 497 4400  
e: [sales@kirkkey.com](mailto:sales@kirkkey.com)

### SPS China

2F, Building 63  
No 421 Hongcao Road, Xuhui District  
Shanghai PRC, 200233  
China

t: +86 (0)21 6040 7398  
f: +86 (0)21 5453 0630  
e: [chinasales@castell.com](mailto:chinasales@castell.com)